# **FBASS15-20**

# Lavoce

15" BASS GUITAR WOOFER

FERRITE MAGNET
STEEL BASKET DRIVER



- 2 INCH COPPER VOICE COIL
- 98 dB/SPL SENSITIVITY
- 400 WATT PROGRAM POWER HANDLING
- TRIPLE ROLL SURROUND
- OVERALL BALANCED AND RICH TONE
- SOLID LOW-END AND TIGHT MID-HIGH'S

### **GENERAL SPECIFICATIONS**

Nominal diameter	mm (in.)	380 (15)	
Nominal impedance	Ω	8	
Minimum impedance	Ω	5,9	
Program power (1)	W	400	
AES Power rating (2)	W	200	
Sensitivity (3)	dB	98	
Frequency range	Hz	40 ÷ 4000	
Voice coil diameter	mm (in.)	51 (2)	
Chassis material	Steel		
Magnet material	Ferrite		
Magnet dimensions	mm	140 x 60 x 17	
OD x ID x h	(in.)	(5.5 x 2.36 x 0.67)	
Coil material	Copper		
Former material	Glass fiber		
Cone material	Water Proof Treated Paper		
Surround material	Polycotton		
Xmax (4)	mm (in.)	4,3 (0.17)	
Xmech (5)	mm (in.)	8,4 (0.33)	
Gap height	mm (in.)	8,2 (0.32)	
Voice coil winding height	mm (in.)	12,6 (0.5)	
Driver displacement volume	I (ft³)	3 (0.1)	

# **SMALL SIGNAL PARAMETERS**

DC resistance	Re	Ohm	5,3
Resonance frequency	Fs	Hz	40
Moving mass	Mms	g (oz)	70 (2.47)
Compliance	Cms	mm/N	0,23
Force factor	BxL	N/A	12,8
Mechanical Q-factor	Qms		8,7
Electrical Q-factor	Qes		0,56
Total Q-factor	Qts		0,53
Equivalent air volume	Vas	I (ft³)	234 (8.26)
Voice coil Inductance	Le	mH	0,70
Diaphragm area	Sd	cm² (in.²)	855 (132.53)
Reference efficiency	Eta 0	%	2,50


### SHIPPING INFORMATION

Net weight	kg (lb.)	4,1 (9.1)
Multipack size (1)	mm	438 x 438 x 204
WxDxH	(in.)	(17.2 x 17.2 x 8)
Multipack weight	kg (lb.)	6,2 (13.6)

# **FREQUENCY RESPONSE**



# DIMENSIONS mm (in.)



(1) Program power is defined as 3 dB greater than AES Power. (2) Tested for two hours using a continuous, band-limited pink noise signal as per AES 2-1984 Rev. 2003. Loudspeaker tested in free air. (3) From T/S parameters, measured with Klippel DA LPM module. (4) The Xmax is calculated as: (Hvc - Hg)/2+ Hg/4. Hvc is the voice coil height and Hg the gap height. (5) Tweet is calculated as: (Hvc - Hg)/2+ (Hg-2). Hvc is the voice coil height and Hg the gap height. (6) Thiele-Small parameters are measured after preconditioning: a) at 20°C- 22°C, 50% humidity for 2 hours; b) by Klippel LSI measurement.

All specifications subject to change without notice\_B.a

